

PMMA block

Product name: Dental PMMA block

Model: 98mm/89mm/95mm

Certificate: CE

Delivery date: 7-10days

Supply capacity: 10,000 per month
After-sales: Return and Replacement

Customized: support

Applicable system: Open/Zirkonzahn /Amann Girrbach system

Product desicription:

We offer PMMA discs designed for CAD/CAM milling machine.

We have Singe-layer PMMA, Multilayer PMMA and Elastic PMMA block.

The diameter is $98 \, \mathrm{mm}$, $95 \, \mathrm{mm}$ or $89 \, \mathrm{mm}$ as request, thickness are 10, 12, 14, 16, 18, 20 and $25 \, \mathrm{mm}, 30 \, \mathrm{mm}$

PMMA Ceradirect PMMA, an acrylic is suitable for long-term temporary restorations.

Ceradirect PMMA is available as monochromatic blank and transparent blank and as a multilayer with shade gradient from dentine toincisal.

A-D shades of PMMA blanks ensure high-end aesthetics and reliable Conventional cutters and trimmers can be used for preparation.

PMMA temporary restorations can be fabricated fully anatomically and can also be veneered with conventional crown and bridge resins.

They are suitable for check-ing the fit and functionality of the actual restoration before it is finished, whereby the tooth-coloured material increases the acceptance of the try-in.

Parameter:

Items	PMMA
Туре	Singe-layer ,Multilayer,Elastic
Thickness	10mm-30mm
System	Roland /Sriona/ VHF /Wieland /

Arum /Amann /zirkonzahn/open
milling system etc.

Physical characteristics:

Density	1.35-1.45g/cm ³
Hardness	85-90 (Shore
	hardness)
Water Absorption	< 0.04%
Antistatic function	Availble
Component	PMMA>99%; Pigment
Flexural strength	>120Mpa
Solubility	<5µg/mm3
Water uptake	<25µg/mm3
Modulus of elasticity	>2200MP

Advantage:

- 1. Excellent abrasion resistance
- 2. Excellent finishing bright surface good polishing performance after milling
- 3. Excellent long-term shade stability and esthetics

Feedback:














CE:

